

Wiha PicoFinish.

The comfortable precision screwdriver.

For TORX® screws.



267P PicoFinish TORX® screwdriver.
Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.													
25673 9	T1	40	2.5	134	9	10							
25674 6	T2	40	2.5	134	9	10							
20122 7	T3	40	2.5	134	9	10							
20123 4	T4	40	2.5	134	9	10							
00566 5	T5	40	2.5	134	9	10							
00567 2	T6	40	2.5	140	18	10							
00568 9	T7	40	2.5	140	18	10							
00569 6	T8	40	2.5	140	18	10							
00570 2	T9	50	3.0	150	18	10							
00571 9	T10	50	3.0	150	18	10							
00572 6	T15	60	3.5	160	18	10							
00573 3	T20	60	4.0	160	18	10							



267PR PicoFinish TORX® MagicSpring® screwdriver.
Handle with rotating cap and rapid-turning zone.
Retaining spring holds TORX® screws in place.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: For setting and tightening TORX® screws in difficult to access areas.

Order-No.							
27729 1	T6	40	2.5	140	18	10	
27730 7	T7	40	2.5	140	18	10	
27731 4	T8	40	2.5	140	18	10	
27732 1	T9	50	3.0	150	18	10	
27733 8	T10	50	3.0	150	18	10	
27734 5	T15	60	3.5	160	18	10	

For TORX PLUS® screws.



267PIP PicoFinish TORX PLUS® screwdriver.
Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.										
29100 6	4IP	40	2.5	134	9	10				
29101 3	5IP	40	2.5	134	9	10				
29102 0	6IP	40	2.5	140	18	10				
29103 7	7IP	40	2.5	140	18	10				
29104 4	8IP	40	2.5	140	18	10				
29105 1	9IP	50	3.0	150	18	10				
29106 8	10IP	50	3.0	150	18	10				
29107 5	15IP	60	3.5	160	18	10				
29108 2	20IP	60	4.0	160	18	10				

Wiha Info



TORX® MagicSpring®.

Simply ingenious – the TORX® MagicSpring® screwdriver from Wiha. Because of the "MagicSpring®" retaining spring made of stainless steel, TORX® screws are held securely in place. An innovation, which will convince each user.

For hex socket screws.



263P PicoFinish hex screwdriver.
Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.								
00519 1	0.7	40	0.028	134	9	10		
00520 7	0.9	40	0.035	134	9	10		
00521 4	1.3	40	0.05	134	9	10		
00522 1	1.5	50	-	144	9	10		
00523 8	2.0	50	5/64	150	18	10		
00524 5	2.5	60	-	160	18	10		
00525 2	3.0	60	-	160	18	10		

263P Zoll PicoFinish hex screwdriver. Inch sizes.
Handle with rotating cap and rapid-turning zone.

Order-No.					
00526 9	1/16	50	144	9	10
00528 3	3/32	60	160	18	10
00530 6	7/64	60	160	18	10
00527 6	1/8	60	160	18	10



264P PicoFinish ball end hex screwdriver.
Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Extra: The ball end enables the user to work at angles up to 25°.

Order-No.						
00531 3	1.3	40	134	0.05	9	10
00532 0	1.5	50	150	-	18	10
00533 7	2.0	50	150	-	18	10
00534 4	2.5	60	160	-	18	10
00535 1	3.0	60	160	-	18	10

264P Zoll PicoFinish ball end hex screwdriver. Inch sizes.
Handle with rotating cap and rapid-turning zone.

Order-No.								
00537 5	1/16	50	150	18	10			
00541 2	5/64	50	150	18	10			
00539 9	3/32	50	150	18	10			
00542 9	7/64	60	160	18	10			
00538 2	1/8	60	160	18	10			
00543 6	9/64	60	160	18	10			
00540 5	5/32	60	160	18	10			

For hex nuts. Chip lifter.



265P PicoFinish hex nut driver.
Handle with rotating cap and rapid-turning zone.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.											
00544 3	1.5	60	2.5	3.0	160	18	10				
00545 0	1.8	60	2.9	3.5	160	18	10				
00546 7	2	60	3.2	4.0	160	18	10				
00547 4	2.5	60	4.0	4.0	160	18	10				
00548 1	3	60	5.0	5.0	160	18	10				
00549 8	3.2	60	5.0	5.0	160	18	10				
00550 4	3.5	60	5.3	6.0	160	18	10				
00551 1	4	60	5.5	6.0	160	18	10				
00552 8	4.5	60	6.2	7.0	160	18	10				
00553 5	5	60	6.8	7.0	160	18	10				
00554 2	5.5	60	7.6	8.0	160	18	10				
00555 9	6	60	8.2	9.0	160	18	10				
00556 6	7	60	9.6	10.0	160	18	10				

265P Zoll PicoFinish hex nut driver. Inch sizes.
Handle with rotating cap and rapid-turning zone.

Order-No.									
00561 0	3/32	60	160	18	2.38	10			
00564 1	7/64	60	160	18	2.78	10			
00559 7	1/8	60	160	18	3.18	10			
00565 8	9/64	60	160	18	3.57	10			
00562 7	5/32	60	160	18	3.97	10			
00560 3	3/16	60	160	18	4.76	10			
00563 4	7/32	60	160	18	5.56	10			
00558 0	1/4	60	160	18	6.35	10			



26810P PicoFinish chip lifter.
Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Handle: Wiha PicoFinish handle.

Application: For lifting tight parts on circuit boards.

Order-No.							
00574 0	1	3.5	50	150	18		5