

NPN General Purpose Transistors by Ascending V_{ce0} (Continued)

Part Type	V_{ce0} (V) Min	V_{ebo} (V) Min	H_{fe}		I_c/V_{ce} (mA/V)	F_t (MHz) Min	Package
			Min	Max			
MPS3393	25		90	180	2/4.5		TO-92
MPS3394	25		55	110	2/4.5		TO-92
MPS3395	25		150	500	2/4.5		TO-92
MPS3396	25		90	500	2/4.5		TO-92
MPS3397	25		55	500	2/4.5		TO-92
MPS3398	25		55	800	2/4.5		TO-92
MPS5172	25	25	100	500	10/10		TO-92
MPS6515	25	40	250	500	2/10		TO-92
MPS6520	25		200	400	2/10		TO-92
MPS6521	25		200	600	2/10		TO-92
MPS6522	25		200	400	2/10		TO-92
MPS6560	25	25	50	200	500/1.0	60	TO-92
PE4010	25	30	200	100	1.0/10		TO-92
PE8050	25	30	65	200	100/1.0	100	TO-92
PN3565	25	30	150	600	1.0/10	40	TO-92
PN5135	25	30	50	600	10/10	40	TO-92
2N2218	30	60	40	120	150/10	250	TO-39
2N2219	30	60	100	300	150/10	250	TO-39
2N2221	30	60	40	120	150/10	250	TO-18
2N2222	30	60	100	300	150/10	250	TO-18
2N3704	30	50	100	300	50/2.0	100	TO-92
2N3705	30	50	50	150	50/2.0	100	TO-92
2N3858	30	30	60	120	2/4.5	250	TO-92
2N3859	30	30	100	200	2/4.5	250	TO-92
2N3860	30	30	150	300	2/4.5	250	TO-92
2N4123	30	40	50	150	2/1.0	250	TO-92
2N4951	30	60	60	200	150/10	250	TO-92
2N4952	30	60	100	300	150/10	250	TO-92
2N4953	30	60	200	600	150/10	250	TO-92
2N4954	30	40	60	600	150/10	250	TO-92
2N4970	30	50	100	350	150/10	200	TO-92
2N5088	30	35	300	900	0.1/5.0	50	TO-92
BSR13	30	60	100	300	150/10	250	TO-236
MMBT2218	30	60	40	120	150/10	250	TO-236
MMBT2219	30	60	100	300	150/10	250	TO-236
MMBT2221	30	60	40	120	150/10	250	TO-236
MMBT2222	30	60	100	300	150/10	250	TO-236
MMBT3566	30	40	150	600	10/10	40	TO-236
MMBT3641	30	60	40	120	150/10	150	TO-236
MMBT3643	30	60	100	300	150/10	250	TO-236
MMBT3704	30	50	100	300	50/1.0	100	TO-236
MMBT3705	30	50	50	150	50/20	100	TO-236
MMBT4123	30	40	5	150	2/1.0	250	TO-236
MMBT5088	30	35	300	900	0.1/5.0	50	TO-236
MPS3704	30	50	100	300	50/20	100	TO-92
MPS3705	30	50	50	150	50/20	100	TO-92
MPS6512	30	40	50	180	2/10		TO-92
MPS6513	30	40	90	180	2/10		TO-92
MPS6532	30	50	30		100/1.0		TO-92
PN2218	30	60	40	120	150/10	250	TO-92
PN2219	30	60	100	300	150/10	250	TO-92
PN2221	30	60	40	120	150/10	250	TO-92
PN2222	30	60	100	300	150/10	250	TO-92