

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

15266-1036

Status:

Active

Overview:

Premo-Flex™ FFC and Etched Polyimide Jumpers

Description:

0.50mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 33 Circuits, 0.102m Cable Length, 0.27mm Cable Thickness, Tin (Sn) Plating



Series

image - Reference only

Documents:

Drawing (PDF)

Product Specification PS-15266-001 (PDF)

Packaging Specification PK-15266-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Crimp Quality Equipment

Overview

Product Name

UPC

Cable

15266

Contacts on opposite sides, Type D

Yes

Premo-Flex™ FFC and Etched Polyimide Jumpers

Premo-Flex™ FFC Jumper

884982445901

Physical

Cable Length

Circuits (Loaded)

Circuits (maximum)

Packaging Type

Pitch - Termination Interface

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

0.102m

33

33

Bag

0.50mm

-40°C to +105°C

N/A

Flat Flex Cable

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A

60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-15266-001

PS-15266-001

SD-15266-001

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

15266Series

Use With

www.molex.com/product/ffcfpc_th.html

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION