

HC-M-KV-T-M32

Order No.: 1646201

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1646201>

Commercial data

GTIN (EAN)	 4 017918 941345
sales group	D092
Pack	10 pcs.
Customs tariff	74153300
Catalog page information	Page 524 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
04/07/2006

[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General data

Cable gland material	Nickel-plated brass
Material, pressure screw	Nickel-plated brass
Cable seal material	Perbunan
Material, O-ring	NBR
Wrench size, union nut	41 mm
Wrench size, support	40 mm

Thread type connection side 1	M32
Length of the connecting thread	8.00 mm
Conductor sealing range	18.00 mm ... 27.00 mm
Clamping range of the strain relief clip	20.00 mm ... 30.00 mm
Degree of protection	IP65
Color	silver
Ambient temperature (operation)	-20 °C ... 80 °C

Diagrams/Drawings

Dimensioned drawing

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;