

**Blade Fuseholders - FKH Stackable Fuseholder
for ATO® Style Blade Fuse Rated 80V**

RoHS





Specifications

- Housing + Adapter:** Out of thermoplastic (UL 94-V0, heat-resistant)
Connections: Leaf spring connector systems, soldering terminals, copper alloy, tinned
Color: Black

Dimensions in mm / Maße in mm

Fuseholder for ATO / FKS size fuses-links. Attachable in X - direction. Rated voltage 80V; crimp terminals.

Sicherungshalter für Sicherungen in ATO / FKS-Größe. Montage in X-Richtung. Nennspannung 80V, Crimp-Kontakte.



Part Number Artikel-Nr.	Description Beschreibung	Contact Temperature Kontakttemperatur
178.6152.000_	Complete	max. 130°C
178.6150.000_	Housing	—
178.6116.250_	Complete with 1.5 - 2.5 mm ²	max. 130°C
178.6152.250_	With 200 mm wiring loop	—
178.6191.000_	Adapter right	—
178.6192.000_	Adapter left	—

Last figure of part number = packaging code, see Section “Packaging Index,” pg. 157.
Corresponding fuse links see Section “Blade Fuses.”
This FKH-Fuseholder can be mounted in row in any number. The fixing adapters are not included in the fuseholder. Please order the adapter separately.