


**General ordering data**

Order No.	8019530000
Part designation	DKPI 35 24VDC/0V
Version	Function component, 24 Vdc , 200 mA , Screw connection
EAN	4008190057022
Qty.	10 pc(s).

Control side

Nominal auxiliary voltage	No
Rated control voltage	P: 24 V DC $\pm 10\%$, N: 2.4...+ 2.4 V DC

General data

Ambient temperature (operational)	-25 °C...+40 °C
Storage temperature	-25 °C...+60 °C
Climate	40°C/93% rel. humidity, no condensation
Connection system	Screw connection
DIN Rail compatibility	TS 35

Load side

Nominal auxiliary voltage	No
Nominal switching current	200 mA
Nominal switching voltage	24 Vdc
Pulse duty factor (gen.)	1:2
Status indicator	Green LED
Voltage drop at max. load	≤ 1.5 V

Dimensions

Width	6 mm
-------	------

Approvals

Approvals institutes	n.a.
----------------------	------

Classifications

ETIM 2.0	EC001504
ETIM 3.0	EC001504

Classifications

eClass 4.1	27-27-09-00
eClass 5.0	27-27-09-90
eClass 5.1	27-27-09-90

Similar products

Order No.	Part designation	Version
8018590000	DKV 35 5VDC 0,5A	Function component, 24 Vdc , 500 mA , Screw connection
8015790000	DKV 35 24VDC 0,5A	Function component, 24 Vdc , 500 mA , Screw connection
8010950000	DKLI 4/35 24VDC	Function component, 24 Vdc , 100 mA , Screw connection