

# Indicator Lights (Neon, LED and Filament Lamp)



UL file E63363

CSA file LR29381

## Colours and voltages:

|                      |                                                                            |
|----------------------|----------------------------------------------------------------------------|
| <b>Neon</b>          | Red, Amber, Green, Clear<br>100/130V (marked 110V), 200/250V (marked 230V) |
| <b>LED</b>           | Red, Yellow, Green<br>2.0/2.2V Resistors for other voltages available      |
| <b>Filament lamp</b> | Red, Amber, Green, (Clear & Blue check availability)<br>6V, 12/14V, 24/28V |

## To create a catalogue number:

Refer to the 2 columns below (terminal and type)

Then state:

Lens colour, voltage and whether neon, LED or filament lamp

| TERM  | TYPE                                                                                                                                                                  | PANEL & °C                       |
|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------|
| L     | <b>L 2951 00</b><br>Chrome bezel available<br><br>S D N FI KEMA EUR S UL CE          | Ø 8.0<br>0.8-1.6<br>page 66      |
| L     | <b>(H) 0568 A(*)</b><br>Deep lens profile<br><br>UL CE (VDE at T100) <b>NEW</b>     | Ø 8.0<br>0.8-3.5<br>page 66      |
| K 2.8 |                                                                                                                                                                       |                                  |
| H 4.8 |                                                                                                                                                                       |                                  |
| L     | <b>(H) 0568 B(*)</b><br>Shallow lens profile<br><br>UL CE (VDE at T100) <b>NEW</b> | Ø 8.0<br>0.8-3.5<br>page 66      |
| K 2.8 |                                                                                                                                                                       |                                  |
| H 4.8 |                                                                                                                                                                       |                                  |
| L     | <b>(L) 0569 AW</b><br><br>UL CE <b>NEW</b>                                         | Ø 9.0<br>0.8-2.5<br>Call factory |
| K 2.8 |                                                                                                                                                                       |                                  |
| H 4.8 |                                                                                                                                                                       |                                  |
| C 6.3 | <b>(C) 0273 00</b><br><br>S D N FI KEMA EUR S UL CE                                | Ø 9.0<br>2.0 max<br>page 66      |
| L     | <b>(C) 0278 00</b><br><br>S D N FI KEMA EUR S UL CE                                | Ø 9.0<br>2.0 max<br>page 66      |
| K 2.8 |                                                                                                                                                                       |                                  |
| H 4.8 |                                                                                                                                                                       |                                  |
| C 6.3 |                                                                                                                                                                       |                                  |

## DIMENSIONS (mm)

