


Technical datasheet: KP1324R4-5847

Specifications:

Input power	Rated 0.01W / Max. 0.03W
Impedance	$150\Omega \pm 15\%\Omega$ (1Vrms at 1kHz)
Frequency Range	300Hz to 3400Hz
Distortion	<5% Max. at 1kHz/1.22Vrms
Out-diameter	$\varnothing 13\text{mm}$
Height	2.8mm
Weight	0.65g
SPL	$110\text{dB} \pm 3\text{dB}$ (387mV at 1kHz)
Buzz and Rattle	Should not be audible buzzes, rattles when the 1.22V sine wave signal swept at frequency range.

Dimensions:



Frequency Response:

