









AMP LOGO LOCATED THIS SURFACE.




MATING CONNECTOR INTERFACE



TYPICAL RECEPTACLE CAVITY SECTION
(DIMENSIONS REFERENCE ONLY)



RECOMMENDED CUTOUT FOR
.060 MAX THICK PANEL



3-DIMENSIONAL MODEL
NTS

	.145	3.68	.868	22.05
.062	1.57	.860	21.84	
.060	1.52	.506	12.85	
.015	0.38	.400	10.16	
.010	0.25	.350	8.89	
.005	0.13	.345	8.76	
IN	MM	IN	MM	

CONVERSION TABLE

METRIC

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLG DEC ± .005 ANGLES MATERIAL NYLON UL 94V-2, NATURAL		DR K. WHITTAKER 11-3-80 CHK R. SWING 11-3-80 APPD R. CARSON 11-4-80 PRODUCT SPEC	DATE 11-3-80	NAME RECEPTACLE, PANEL MOUNT, 4 CIRCUIT, .062 PIN AND SOCKET
FINISH NATURAL	APPLICATION SPEC	SIZE D 00779	FRSCH NO 770441	DRAWING NO 770441
WEIGHT	SCALE 5:1	SHEET	1 OF 1	