

**Ratings:**  
 Current 4A  
 Voltage 150 V  
 Wire Size 28-20AWG  
 Test Voltage 1.25 kV

**Rated Cross Section:**  
 Single Wire (solid) .5mm<sup>2</sup>  
 Stranded Wire (flexible) on request  
 Stranded Wire with Ferrules on request

**Dimensions:**  
 Spacing 2.5mm (2.54mm)  
 PCB Hole Diameter 1.1mm (2x)  
 Stripped Length 5.0mm

**Materials:**  
 Insulating Material PA  
 Flammability UL94V-0  
 Temperature -30°C/+105°C  
 Tension Spring Stainless Steel  
 Contact Cu  
 Color Slade Gray (Orange)

