


MICRO SWITCH

A DIVISION OF AMTHERPOLIS-HONEYWELL REGULATOR COMPANY
PINEBROOK, NEW JERSEY

FED. MFR. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
BAFI-3CNXI



NOTE-

1-6-32 NC X .218^{REF} BINDER HEAD TERMINAL SCREWS (STAKED).

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS (BOTH PLUNGERS)

OPERATING FORCE --- 1 1/2 LBS. MAX.

OVERTRAVEL --- .219 MIN.

SWITCH-BASIC REPLACEMENT-BA-3CX716

ELECTRICAL DATA

CONTACT ARRANGEMENT
SINGLE POLE DOUBLE THROW
MAINTAINED CONTACT

BREAK DISTANCE
.036 MIN.

CODE L19/ 15A-125, 250 OR 480 VAC
3/4HP-125 VAC; 1 1/2HP-250 VAC
1/2A-125 VDC; 1/4A-250 VDC

SCALE-FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT

BAFI-3CNXI

M

DRAWING NUMBER

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE

ISSUE