







REV.	DATE	DESCRIPTION
NC	12/27/03	INITIAL RELEASE



RECOMMENDED CABLE STRIPPING DIMENSIONS



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .178"
 2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"
 3. MAX. PANEL THICKNESS = 6.5mm

8	HEX NUT	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	PART DESCRIPTION
7	LOCK WASHER	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	DRAWN	G.R.S.	12/27/03
6	FERRULE	BRASS	NICKEL	1	0.5 - 8mm ± 0.20mm	CHECKED		
5	SLEEVE	DELRI	NATURAL	1	8 - 30mm ± 0.40mm	ISSUED		
4	GASKET	RUBBER	RED	1	30 - 120mm ± 0.50mm	SHEET	1 OF 1	
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:	CAD FILE		
2	INSULATOR	TEFLON	NATURAL	1	.020 - .315 = ± 0.007"	DWG. NO.	112719.DWG	
1	BODY	BRASS	NICKEL	1	.315 - 1.180 = ± 0.015"	REV.	NC	
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	SIZE	A	
						SCALE	NA	

Amphenol Connex

BNC BULKHEAD CRIMP JACK
(FOR RG-174/U, 188A/U, 316/U CABLE)

112719