

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
N		REVISED PER ECO-16-001548	08MAR2016	AP	DG

D

C

B




A

D

C

B

A



- △ HOUSING: FLAME RETARDANT 94V-O RATED THERMOPLASTIC; COLOR: BLACK.
- △ SHELL: CARBON STEEL.
- △ CONTACTS: PHOS. BRONZE.
- △ INSERTS & BOARDLOCKS: BRASS
- SCREWLOCKS: ZINC.
- 5. NOTE DELETED.
- △ SHELL: .000200 MIN TIN OVER .000100 MIN COPPER.
- △ INSERTS: UNPLATED, SCREWLOCKS: UNPLATED, BOARDLOCKS: TIN OVER COPPER.
- △ CONTACTS: GOLD FLASH FOR LENGTH OF .100 MIN FROM MATING END, .000100-.000200 BRIGHT TIN OR BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
- △ CONTACTS: .000030 GOLD FOR LENGTH OF .100 MIN FROM MATING END, .000100-.000200 BRIGHT TIN OR BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
- 10. NOTE DELETED.
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- △ RECOMMENDED SCREWLOCK IS 5747877-3 WITH RETENTION INSERTS.
- △ .110 MAX IN SHELL TAB CLINCH AREAS.

SUPERSEDED BY 1-747301-6	WITH FEMALE SCREWLOCKS	△ 9	.170	2-747709-1
SUPERSEDED BY 2-747709-0	WITH INSERT BOARDLOCKS	△ 9	.125	2-747709-0
OBSOLETE		△ 8	.125	1-747709-9
OBSOLETE		△ 9	.250	1-747709-8
SUPERSEDED BY 1-747301-6	WITH FEMALE SCREWLOCKS	△ 8	.250	1-747709-7
OBSOLETE		△ 9	.170	1-747709-6
OBSOLETE		△ 8	.170	1-747709-5
OBSOLETE		△ 9	.125	1-747709-4
OBSOLETE		△ 8	.125	1-747709-3
OBSOLETE		△ 9	.250	1-747709-2
OBSOLETE		△ 8	.250	1-747709-1
OBSOLETE	WITH THREADED INSERTS	△ 9	.170	1-747709-0
SUPERSEDED BY 747301-8		△ 8	.170	747709-9
SUPERSEDED BY 747301-7		△ 9	.125	747709-8
OBSOLETE		△ 8	.125	747709-7
OBSOLETE		△ 9	.250	747709-6
OBSOLETE		△ 8	.250	747709-5
OBSOLETE		△ 9	.170	747709-4
OBSOLETE	WITH .120 DIA. HOLE	△ 8	.170	747709-3
OBSOLETE		△ 9	.125	747709-2
OBSOLETE		△ 8	.125	747709-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 2-27-85	TE Connectivity	
		CHK J. GERACE 2-27-85		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. BAER/R. BRANDT 2-27-85	NAME	
		PRODUCT SPEC	RECEPTACLE ASSEMBLY, SIZE 4, 37 POS., VERTICAL, .026 DIA. DUPLEX PLATED POSTS, FRONT SHELL, AMPLIMITE	
MATERIAL	FINISH	APPLICATION SPEC	RESTRICTED TO	
		WEIGHT	CUSTOMER DRAWING	