







A



SMT



DIP



NOTES:

- Insulator: Nylon PA9T
- Contacts: Phosphorbronze, $t=0.25\text{mm}$
- Shell: Brass $t=0.3$ / Finish: Nickel Plated
- Withstanding Voltage: 500V AC (1 min)
- Insulation Resistance: 1000M min.
- Rated Voltage and Current: 1.5A at 250V AC min.

Scale	1:1						Name	Item No. A-USB-A-LP-R (Version 1.1, DIP) A-USB-A-LP/SMT-R (Version 1.1, SMT) A-USB/2-A-LP-R (Version 2.0 DIP) A-USB/2-A-LP-SMT-R (Version 2.0, SMT)	
TOLERANCE						Drawn	10.19.11		Chappell
X.X	±0.40					Approved			
X.XX	±0.25								
X.XXX	±0.15								
Angle	±3°								
								Drawing No.	rev00
								Replace	
			Modification	Date	Name				



H