

New

MT series

Sealed selector switch

11/16 threaded bushing



- ☐ Environmentally sealed toggle switch (IP68)
- ☐ Multiple single pole functions available
- ☐ Various contact materials that allow for usage from dry circuit applications up to 6A 125VAC, 3A 250VAC

SPECIFICATIONS

- Current/voltage rating with resistive load :

Contact	Maximum	Minimum	Level*
Silver (A)	3A 250VAC - 6A 125VAC - 4A 30VDC	50mA 10VDC	III and IV
Silver, gold plated (AD)	3A 250VAC - 6A 125 VAC - 4A 30VDC Gold plating withstands up to 100mA 30VDC	10mA 50mV 10μA 5V	I to IV
Brass, gold plated (CD)	0,4 VA at 20VAC or DC	10mA 50mV 10μA 5V	I and II

- Initial contact resistance : 10 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
 - 1.000 Vrms 50 Hz min. between terminals
 - 1.500 Vrms 50 Hz min. between terminals and frame
- Contact bounce : 2 ms max.
- Electrical life at full load : 50.000 cycles
- Low level or mechanical life : 100.000 cycles
- Operation temperature: -40°C to +85°C



MATERIALS

- Actuator : 6/6 Nylon
- Bushing : brass, nickel plated
- Contacts
 - A : silver
 - AD : silver, gold plated
 - CD : brass, gold plated
- Terminal seal : epoxy


MT series

Sealed selector switch

MT	G																																			
SERIES		<table><tr><td colspan="4">Electrical function</td></tr><tr><td>6</td><td>ON</td><td>-</td><td>ON</td></tr><tr><td>9</td><td>ON</td><td>OFF</td><td>ON</td></tr><tr><td>7</td><td>MOM</td><td>OFF</td><td>MOM</td></tr><tr><td>8</td><td>ON</td><td>OFF</td><td>MOM</td></tr><tr><td>2</td><td>ON</td><td>-</td><td>MOM</td></tr></table>	Electrical function				6	ON	-	ON	9	ON	OFF	ON	7	MOM	OFF	MOM	8	ON	OFF	MOM	2	ON	-	MOM		<table><tr><td colspan="2">Contact material</td></tr><tr><td>A</td><td>Silver</td></tr><tr><td>AD</td><td>Gold plated silver</td></tr><tr><td>CD</td><td>Gold plated brass</td></tr></table>	Contact material		A	Silver	AD	Gold plated silver	CD	Gold plated brass
Electrical function																																				
6	ON	-	ON																																	
9	ON	OFF	ON																																	
7	MOM	OFF	MOM																																	
8	ON	OFF	MOM																																	
2	ON	-	MOM																																	
Contact material																																				
A	Silver																																			
AD	Gold plated silver																																			
CD	Gold plated brass																																			
	<table><tr><td colspan="2">Finish</td></tr><tr><td>Blank</td><td>bright chrome finish</td></tr><tr><td>G</td><td>Matt black finish (standard)</td></tr></table>	Finish		Blank	bright chrome finish	G	Matt black finish (standard)		<table><tr><td colspan="2">Terminals</td></tr><tr><td>1</td><td>Straight P.C.</td></tr><tr><td>2</td><td>Solder lug</td></tr></table>	Terminals		1	Straight P.C.	2	Solder lug		<table><tr><td colspan="2">Actuator color</td></tr><tr><td>2</td><td>Black</td></tr><tr><td colspan="2">Consult factory for other options.</td></tr></table>	Actuator color		2	Black	Consult factory for other options.														
Finish																																				
Blank	bright chrome finish																																			
G	Matt black finish (standard)																																			
Terminals																																				
1	Straight P.C.																																			
2	Solder lug																																			
Actuator color																																				
2	Black																																			
Consult factory for other options.																																				



Sealed Selector with P.C. terminals



Mounting accessories : standard hardware supplied with all models one hex nut 20.64 (.813) across flats, and one sealing gasket



Packaging unit : 25 pieces or 50 pieces depending on model