


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			A	REV PER ECR 07-017430	01AUG07	JR
						APVD
						TM

AMP WIRE RANGE	 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED



- 1 STAMP "AMP 12-10*", LOCATION APPROX AS SHOWN.
- 2 TONGUE THICKNESS IS 1.0±0.05
- 3 APPLIES TO EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 4 WIRE INSULATION DIA RANGE 3.81-6.35
- 5 BODY - COPPER PER ASTM B-152
SLEEVE - PVC
- 6 BODY - TIN PL PER ASTM B-545
SLEEVE - COLOR - YELLOW
- 7 105°C MAX OPERATING TEMPERATURE.
- 8 600 VOLT MAX
- 9 2.62-6.64mm² [5,180 - 13,100 CMA]
SOLID OR STRANDED

500	LOOSE PIECE	130677
QTY	PACKAGE TYPE	PART NO
500		
QTY		
LOOSE PIECE		
130677		
QTY		
PACKAGE TYPE		
PART NO		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 01AUG07	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm INCHES		CHK T MICHELUTTI 01AUG07				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHELUTTI 01AUG07	NAME TERMINAL RING TONGUE, PLASTI-GRIP, WIRE SIZE 12-10			
MATERIAL		PRODUCT SPEC	-			
FINISH		APPLICATION SPEC	-			
-		WEIGHT	-			
CUSTOMER DRAWING		SCALE	4:1			
SHEET		1 OF 1				REV
A		A				