

# PANASONIC 12 VOLT LEAD-ACID BATTERIES



| Part Number       | Volts   | Capacity<br>20Hr. Rate | Dimensions (Inches) |       |                     | Weight (Lbs) | Cross Reference                   | Termination   |
|-------------------|---|------------------------|---------------------|-------|---------------------|--------------|-----------------------------------|---------------|
|                   |   |                        | Length              | Width | Height<br>Inc. Term |              |                                   |               |
| LEAD-12V-1.3P     | 12  | 1.3                    | 3.82                | 1.87  | 2.16                | 1.30         | LC-R121R3P, LCR12V1.3P            | .187 TAB      |
| LEAD-12V-2P       | 12  | 2.0                    | 6.97                | .94   | 2.52                | 1.40         | LC-T122PU                         | .187 TAB      |
| LEAD-TA122PU      | 12  | 2.0                    | 7.17                | .94   | 2.42                | 1.40         | LC-TA122PU                        | PRESSURE      |
| LEAD-12V-2.2P     | 12  | 2.2                    | 6.97                | 1.34  | 2.60                | 1.76         | LC-R122R2P, LCR12V2.2P            | .187 TAB      |
| LEAD-12V-3.4P     | 12  | 3.4                    | 5.28                | 2.64  | 2.60                | 2.65         | LC-R123R4P, LCR12V3.4P            | .187 TAB      |
| LEAD-12V-4P       | NLA — USE LEAD 12V-5P   |                        |                     |       |                     |              | LC-RB124P                         |               |
| LEAD-12V-5P       | 12  | 5.0                    | 3.54                | 2.76  | 4.26                | 4.25         | LC-R125P, LCR12V5P                | .187 TAB      |
| LEAD-12V-6.5P     | NLA — USE LEAD 12V-7.2P                                       |                        |                     |       |                     |              | LCR-12V-6.5P                      |               |
| LEAD-12V-6.5P-250 | NLA — USE LEAD 12V-7.2P-250                                   |                        |                     |       |                     |              | LCR-12V-6.5P1                     |               |
| LEAD-12V-7.2P     | 12  | 7.2                    | 5.95                | 2.54  | 3.94                | 5.45         | LC-R127R2P, LCR12V7.2P            | .187 TAB      |
| LEAD-12V-7.2-250  | 12  | 7.2                    | 5.95                | 2.54  | 3.94                | 5.45         | LC-R127R2P1                       | .250 TAB      |
| LEAD-12V-12P      | 12  | 12.0                   | 5.95                | 3.86  | 3.90                | 8.30         | LC-R1212P, LCR12V12PF, LC-RA1212P | .250 TAB      |
| LEAD-12V-17P      | 12  | 17.0                   | 7.13                | 2.99  | 6.57                | 14.3         | LC-RC1217P, LCR12V17CP, LC-RD121D | NUT & BOLT    |
| LEAD-12V-20P      | 12  | 20.0                   | 7.13                | 2.99  | 6.57                | 14.5         | LC-X1220P                         | NUT & BOLT    |
| LEAD-12V-24PB     | NLA — USE LEAD 12V-28PB (NOTE REVERSED POSITIVE AND NEGATIVE) |                        |                     |       |                     |              | LCR-12V-24P                       |               |
| LEAD-12V-28PB     | 12  | 28.0                   | 6.50                | 4.90  | 7.10                | 24.30        | LC-X1228P                         | NUT & BOLT    |
| LEAD-12V-28PTP    | 12  | 28.0                   | 6.50                | 4.90  | 6.90                | 24.30        | LC-X1228AP                        | THREADED POST |
| LEAD-12V-33P      | 12  | 33.0                   | 7.70                | 5.12  | 7.09                | 26.5         | LC-LA1233P, LCL12V33AP            | NUT & BOLT    |
| LEAD-12V-38P      | NLA — USE LEAD 12V-42P  |                        |                     |       |                     |              | LCR-12V-38P                       |               |
| LEAD-12V-42P      | 12  | 42.0                   | 7.75                | 6.49  | 7.08                | 35.20        | LC-X1242P                         | NUT & BOLT    |
| LEAD-12V-42PTP    | 12  | 42.0                   | 7.75                | 6.49  | 7.08                | 35.20        | LC-X1242AP                        | THREADED POST |
| LEAD-12V-65P      | 12  | 65.0                   | 13.78               | 6.54  | 6.89                | 44.1         | LC-L1265P, LCL12V65P, LC-X1265P   | NUT & BOLT    |
| LEAD-12V-100P     | 12  | 100.0                  | 16.03               | 6.82  | 9.29                | 72.8         | LCR12V100AP, LC-XA12100P          | NUT & BOLT    |

| Part Number              | Volts | Capacity<br>20Hr. Rate | Dimensions (Inches) |       |                     | Weight (Lbs) | Cross Reference | Termination |
|--------------------------|-------|------------------------|---------------------|-------|---------------------|--------------|-----------------|-------------|
|                          |       |                        | Length              | Width | Height<br>Inc. Term |              |                 |             |
| <b>HIGH POWER SERIES</b> |       |                        |                     |       |                     |              |                 |             |
| LEAD-UPRW1220P           | 12    | 20.0                   | 5.51                | 1.51  | 3.99                | 2.98         | UP-RW 1220P     | .187 TAB    |
| LEAD-UPRW1220P-250       | 12    | 20.0                   | 5.51                | 1.51  | 3.99                | 2.98         | UP-RW1220P1     | .250 TAB    |
| LEAD-UPRW1245P           | 12    | 45.0                   | 5.95                | 2.54  | 3.99                | 5.73         | UP-RW1245P      | .187 TAB    |
| LEAD-UPRW1245P-250       | 12    | 45.0                   | 5.95                | 2.54  | 3.99                | 5.73         | UP-RW1245P1     | .250 TAB    |

**NOTES**

LEAD ACID