

1608L1-Series

MSA-compatible 4.25Gb/s Cooled DWDM DFB TOSA



Product Brief



Description

The 1608-Series 4.25 Gb/s transmitter optical subassembly (TOSA) integrates a high-speed laser, a monitor photodiode and a micro-TEC in a small form-factor metallized ceramic package. It is designed for use in small form-factor pluggable (SFP) transceivers and other types of optical modules for high-speed telecommunication and data applications including WDM 4X Fiber Channel and 4G Gigabit Ethernet.

The 1608-Series is available in the full range of C band ITU-T wavelengths operating at 4.25 Gb/s per channel. The device exhibits excellent wavelength stability, supporting operation at 100 GHz channel spacing over 15 years (assuming an end-of-life aging condition of $<\pm 90$ pm), with low hazard rates (~ 100 FIT wearout over 20 yrs.).

1608L1xx is the standard commercially available variant.

Features

- Ultra small form factor 9-pin MSA DFB TOSA
- Data rates up to 4.25Gb/s
- For use up to 80 km (1600 ps/nm) at 4.25 Gb/s
- +3 dBm minimum optical output power
- Wavelength selectable to C-band ITU-T grid wavelengths
- Suitable for use in 100GHz channel spacing DWDM systems
- Temperature stabilized; can also be operated in partially cooled mode for CWDM applications
- Maximum power consumption less than 0.25W
- LC receptacle
- 25 Ω single-ended data input
- Case operating temperature range: -5 to +75°C

For product information and a complete list of distributors, please go to our web site: www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries.

CyOptics and the CyOptics logo are trademarks of CyOptics, Inc. in the United States and other countries.

Data subject to change. Copyright © 2005-2013 CyOptics, Inc. All rights reserved.

AV02-4120EN - June 5, 2013

