

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS THE PROPERTY OF TE CONNECTIVITY AND IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TE CONNECTIVITY. ANY UNAUTHORIZED DISCLOSURE OR USE OF THIS INFORMATION IS PROHIBITED AND WILL BE SUBJECT TO LEGAL ACTION.

1583004

THIS DRAWING IS A CONTROLLED DOCUMENT.

TOOL NUMBER											USED ON	CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
WIRE SIZE mm ² [AWG]													
INSULATION DIAMETER mm [in.]												CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
INSUL. ADJ.													
FLIP LOCATOR												CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
STRIP LENGTH mm [in.]													
CRIMP HEIGHT mm [in.]												CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
CONTACT PART NUMBERS													
LOOSE PIECE												CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
STRIP FORM													
91564-1 91564-3												Type III+ (yellow) (red)	114-10004
0.20-0.56 [24-20] 0.05-0.15 [30-26] 0.12-0.22 [26-24]													
1.02-2.03 [.040-.080] 1.02-1.52 [.040-.060] 0.89-1.40 [.035-.055]												TYPE VI INSULATION GRIP CONTACTS	114-10007
NO NO NO													
3.55-4.75 [.140-.187] 4.37 [.172]												TYPE VI INSULATION GRIP CONTACTS	114-10007
1.00 ± 0.05 [.039 ± .002] 0.79 ± 0.04 [.031 ± .002]													
66103-[] 66593-[] 66596-[] 66105-[] 170246-[] 66594-[] 66429-[] 170248-[] 66595-[] 66428-[]												TYPE VI INSULATION GRIP CONTACTS	114-10007
66107-[] 66237-[] 170252-[] 66109-[] 170250-[]													
66591-[]												TYPE VI INSULATION GRIP CONTACTS	114-10007
66592-[]													
66102-[] 66583-[] 66586-[] 66104-[] 170245-[] 66584-[] 66425-[] 170247-[] 66585-[] 66424-[]												TYPE VI INSULATION GRIP CONTACTS	114-10007
66106-[] 170249-[] 66108-[] 170251-[]													
2844982-1												TYPE VI INSULATION GRIP CONTACTS	114-10007
0.30 [22] 0.60-0.80 [20-18]													
1.27-2.79 [.050-.110] 1.27-2.79 [.050-.110]												TYPE VI INSULATION GRIP CONTACTS	114-10007
NO NO													

1. LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.
2. AMP and CERTI-CRIMP are trademarks.
3. -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

						mm				APVD 22FEB2012		 TE Connectivity			
								0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± -		B.A. WOLFE					
										NAME		CERTI-CRIMP II TOOL DATA SHEET			
						ANGLES ± -						MULTIMATE CONTACT FAMILY OPEN BARREL			
- SEE SHEET 1				-		-		-							
P	LTR	REVISION RECORD		DATE	DWN	APVD	SURFACE TEXTURE			SCALE	SIZE	DRAWING NO	SHEET	OF	REV
										-	A1	1583004	2	2	D1