


37316300410 - 373 Series



Series: 373

Fuse 373 Datasheet

The 373 Series are TR5®, sub-miniature, fast-acting type, 250V rated fuses, designed in accordance to UL 248- 14.

Features:

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance, Shocksafe casing
- Vibration resistant
- Halogen free
- CCCe for China import

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

Feedback

Electrical Characteristics		Technical Resources	Environmental Info
Property (Mouseover for details)		Value	
Ampere Rating (A)		6.3	
Nominal Melting I²T (A²sec)		9.1	
Interrupting Rating		50A@250VAC	
Min Operating Temp °C		-40	
Max Operating Temp (°C)		85	
Moisture Sensitivity Level		MIL-STD-202 Method 106	
Nominal Power Dissipation (W)		1000	
Nominal Voltage Drop (mV)		115	
Nominal Cold Resistance (Ohms)		0.01331	
Opening		Fast-Acting (F)	
Package Size		TR5 (8.5x8mm)	
VAC (V)		250	

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).

Mobile Site

- About Littelfuse
- About Littelfuse

Conflict Free Statement

History

Investor Relations

Legal

Press Room

Privacy Statement

Supply Chain Transparency

Website Feedback

- Explore Littelfuse
- Capabilities Brochures

Careers

Check Distributor Stock

Competitor Cross Reference

Industries

Order Samples

Products

Services

- Technical Resources
- Application Designs

Education

FAQs

iDesign™

Littelfuse University

Product Catalogs

Quality Documents

Technical Documents