

DK Cable junction boxes



cable entry via elastic membranes and integrated M 20 thread

- rated insulation voltage: 400 V
- degree of protection: IP 55
- degree of protection: IP 65 (ADM)
- material: thermoplastic
- colour: grey, RAL 7035





DN 2000

cable entry: 8 membranes, closed
(sealing range: Ø 3-12 mm)
integrated M 20 thread
without terminals





DN 2030

included cable entry 3 ADM 20,
(sealing range: Ø 6.5-13.5 mm)
8 membranes, closed
(sealing range: Ø 3-12 mm)
integrated M 20 thread
without terminals



DN 2035

5-pole,
per pole 6 x 1.5 mm² sol, 4 x 2.5 mm² sol,
3 x 4 mm² sol
included cable entry 3 ADM 20,
(sealing range: Ø 6.5-13.5 mm)
8 membranes, closed
(sealing range: Ø 3-12 mm)
integrated M 20 thread



Cable gland
degree of protection: IP 65
colour: grey, RAL 7035
material: thermoplastic

ADM 20

ISO thread sealing range
M 20 x 1.5 Ø 6.5-13.5 mm