




REV. 2

DCO 63333


COIL: @ 25°C
 RESISTANCE 390 OHMS ±10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.0 VDC @ 25°C
 MUST RELEASE 1.4 VDC @ 25°C

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 15 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 5 MS MAX.
 BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
 2 AMP 28 VDC RESISTIVE

DR. R.B. 9/27/93

CK. TLG 10-24-00

CII Technologies™
 advanced control electronic solutions

CUST. CII STD

CUST. NO. REV.

"SR" RELAY

SRBW-4C-24B