





TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.GX00
15	39.14	33.32	25.18	25.12	19.18	D15P24A.GX00
25	53.03	47.04	39.12	38.84	33.12	D25P24A.GX00
37	69.32	63.50	55.68	55.30	49.68	D37P24A.GX00

Protection: 4 ---> flash AU
6 ---> 0.76µ AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.GX00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A.GX00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A.GX00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A.GX00LF

Protection: 4 ---> flash AU
6 ---> 0.76µ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

rev	ecn no	dr	date
C	-	JOU	1996/09/09
E	LS05-001	MPE	2005/03/11
F	LS05-0056	MPE	2005/06/27
G	LS06-0019	LGO	2006/02/07
H	LS06-0097	LGO	2006/07/29
J	I10-0038	NG	2010-02-03

www.fciconnect.com			surface	ISO 1302	tolerance std	ISO 406	ISO 1101	projection	European Views
			TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	LELEON	1992/09/10	ANGULAR		0.X		±0.1	size	A3
Eng	PESSON	1992/09/10	LINEAR		0.XX		±0.1	Scale	2
Chr	NIRMAL.G	2010-02-03	0.XX	±2°	0.XXX		±0.1	ECN	I10-0038
Appr	SUDHIR.V	2010-02-03	Product family			D-SUB			Spec ref -
FCI			MALE CONNECTOR DELTA D ST			C01-8646-0101			Rev. J
straight,solder type for			-			CUSTOMER sheet 1 of 1			