



JKL LAMP PART NUMBER	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mArms)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF26240-24B	LCD HIGH OUTPUT WHITE 11000°k RGB	1250 @ 0°C	505	5	30,000 ± 10%	20,000

\* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

METRIC		DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION			
 THIRD ANGLE PROJECTION		TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0 2 PL +/- 0 ANGLE +/- 0		<b>TITLE</b> MINIATURE COLD CATHODE FLUORESCENT LAMP			
DRAWN BY L. WENGSTROM		APPVD BY DATE FD 10/17/00		SIZE <b>A</b>	FSCM NO. <b>55335</b>	DRAWING NO. <b>BF26240-24B</b>	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE		RELEASED DATE 5/22/00	REVISION DATE 10/17/00	REV. NO. A	SHEET 1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
A	DIM LINE CORRECT. AND 240+/-5.0 TO 240+/-3.0	10/17/00
	RELEASED	5/22/00

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF26240-24B](#)