








Standard Heat Sinks for Medium and High Power Applications

Type	Profile (mm)	Performance for Tropical Climates Thermal Resistance — °C/w									
		Plain or Alocromed Finish (1,3)					Matt Black Anodised Finish (2)				
		50mm	75mm	100mm	125mm	150mm	50mm	75mm	100mm	125mm	150mm
38DN		2.4	2.0	1.7	1.6	1.4	2.1	1.7	1.5	1.4	1.2
39DN		1.4	1.0	0.75	0.70	0.65	1.2	0.85	0.65	0.60	0.57
40DN		2.1	1.5	1.3	1.2	1.1	1.6	1.3	1.2	1.1	1.0
41DN		1.7	1.4	1.2	1.1	1.0	1.5	1.2	1.0	0.93	0.90
42DN		3.5	2.9	2.3	2.1	1.8	3.0	2.5	2.0	1.8	1.6
43DN		2.8	2.1	1.7	1.6	1.4	2.4	1.8	1.5	1.3	1.2
44DN	 HOLE SIZE 3.30 Ø TEE SLOTS SUIT M4 CAGE NUTS (PT NO 400)	2.3	1.8	1.5	1.4	1.25	1.8	1.4	1.2	1.1	1.0

CUSTOM DESIGNS: Heat sinks with profiles other than those shown can be offered to suit your specific requirements

ACCESSORIES: See our range of accessories at back of brochure