

AULT SPECIFICATIONS

0.3-2 VA Wall Plug Series

INPUT

Voltage	120 VAC
Line Frequency	60 Hz
Configuration	North American Wall Plug, No Ground

OUTPUT

<i>Model Number</i>	<i>Rated Output Volts AC</i>	<i>Output Current Amps</i>	<i>Max VA</i>
T28-030100-A000G	3	0.10	0.3
T28-030200-A000G	3	0.20	0.6
T28-040100-A000G	4	0.10	0.4
T28-040200-A000G	4	0.20	0.8
T28-040250-A000G	4	0.25	1.0
T28-050400-A000G	5	0.40	2.0
T28-060200-A000G	6	0.20	1.2
T28-060250-A000G	6	0.25	1.5
T28-090100-A000G	9	0.10	0.9
T28-120166-A000G	12	0.17	2.0
T28-150100-A000G	15	0.10	1.5
T28-240050-A000G	24	0.05	1.2

ELECTRICAL

Topology	Step Down AC/AC Transformer
Dielectric Withstand	1500 VAC primary-secondary
Protection	Energy Limiting
EMI	Meets FCC Class B
CE	NA

SAFETY APPROVALS

UL1310, CSA22.2-223

ENVIRONMENTAL

Operating Temperature	0° to 40° C with no derating
Storage Temperature	-30° to +85° C
Relative Humidity	5% to 95% non-condensing
Altitude	0 - 10,000 feet
Cooling	Convectional non-vented case

MECHANICAL

Case and Dimensions	T28 - North American Wall Plug 50 L X 36 W X 32 H (mm) 2.0 L X 1.4 W X 1.3 H (in)
Case Material	Black 94V1 Polycarbonate
Weight	4 ounces, 115 grams, (excluding cord)
Cord and Connectors	6 ft., 2 Conductor, 22-24 AWG, Ault #3 Connector Other connectors are also available

WARRANTY

1 Year