

Distributed by:



www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

1008-09 S I K S S




1 2 3 4 5 6

- 1 NO. OF PINS : 09, 15, 25, 37
- 2 CONTACT TYPE : P-Male S-Female
- 3 SHELL PLATED : T - Tin shell
- 4 INSULATOR COLOR : B-blue K-black Y-yellow
- 5 MOUNTING TYPE : S-With jack screws & board lock
R-With UNC#4-40 insert & board lock
separate with screws
O-Other options under requirements
- 6 CONTACT PLATED : S-Selective gold plated
G-Gold plated

FEMALE



MALE



D-SUB RIGHT ANGLE TYPE (7.2mm)

Specifications:

Contact Resistance: 30mΩmax. at DC 100mA
Insulator Resistance: 1000MΩmin. at DC 500V
Current Rating: 5 AMP

Dielectric Withstanding

Voltage: AC 1000V For 1 minute
Operating Temperature: -55°C~+105°C
Contact: Brass or Phosphor Bronze
Housing: PBT & 30% Glass Fiber (UL 94V-O)

Dimension

Position	A	B	C	D
9	16.92	24.99	30.81	16.33
15	25.25	33.32	39.14	24.66
19		39.03	44.80	29.92
23		44.36	50.30	35.18
25	38.96	47.04	53.04	38.38
37	55.42	63.50	69.32	54.84
50	52.86	61.11	66.90	52.34