

SDS-Plus Drill Bits



Features carbide tipped drill bit tip and innovative 4-fold spiral flute for rapid drilling, dust removal and wall friction.

Safety note : when using drill bits with length above 460mm, pre-drill to a depth of 150mm.

490642

Cutting Diameter	Overall Length	Working Length		Price Each
(mm)	(mm)	(mm)	Order Code	
5	110	50	135-8690	
5	160	100	135-8670	
5.5	110	50	135-8671	
5.5	160	100	135-8672	
6	110	50	135-8691	
6	160	100	135-8673	
6	210	150	135-8703	
7	110	50	135-8675	
7	160	100	135-8676	
7	210	150	135-8715	
8	160	100	135-8677	
8	210	150	135-8678	
8	260	200	135-8696	
10	160	100	135-8679	
10	210	150	135-8697	
10	260	200	135-8680	
10	460	400	135-8699	
10	1000	950	135-8707	
12	160	100	135-8681	
12	210	150	135-8700	
12	260	200	135-8692	
12	460	400	135-8701	
12	1000	950	135-8708	
13	160	100	135-8682	
14	160	100	135-8693	
14	210	150	135-8684	
14	310	250	135-8702	
14	1000	950	135-8709	
15	160	100	135-8685	
16	210	150	135-8705	
16	310	250	135-8706	
16	450	400	135-8695	
16	1000	950	135-8710	
18	1000	950	135-8711	
20	1000	950	135-8712	
22	1000	950	135-8713	
25	450	400	135-8694	
25	1000	950	135-8714	