

Within Series Adaptor 34_MCX-50-0-2/111_N

Description

Bulkhead adaptor jack/jack
MCX jack (female) / MCX jack (female)

Interface standard
Series MCX - IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz
Frequency range	DC to 1.5 GHz
Return loss	≥ 30 dB
	1.5 to 6 GHz
	≥ 20 dB

Mechanical Data

Number of matings	500
Weight	0.0021 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS)	compliant

Material Data

Interface - MCX jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Interface - MCX jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00013612
Mounting hole	DOU-00008768

Ordering Information

Single package 34_MCX-50-0-2/111_NE