


Pluggable Terminal Strips Plug in

Features

- Moulded from PA6
- White colour
- Easily cut to size
- Self extinguishing
- IMQ, CE Approved



Notes: UL94-VO (160°C) flame retardant version available on request.
Available pre-cut to length for volume orders.

Specification

Voltage (max)	450Vac
Working temperature	85°C
Short period	110°C
No. of poles	12
Moulding	UL94-V2 Self-extinguishing Polyamide 6
Conducting bush	Brass
Screws	6µ Zinc, colour passivated and tropicalised

Type No.	Size	Length	Width	Height	Fixing Holes	Insert diameter	Fixing hole pitch	Screw	Max Current
CTSN431/12M	8mm/6A	94.8mm	16mm	15.3mm	2.5mm	2.9mm	8.0mm	M3	17.5A
CTSN431/12F	8mm/6A	94.8mm	16mm	15.3mm	2.5mm	2.9mm	8.0mm	M3	17.5A
CTSN433/12M	10mm/10A	119mm	20.3mm	16.4mm	3.2mm	3.4mm	10.0mm	M3	24A
CTSN433/12F	10mm/10A	119mm	20.3mm	16.4mm	3.2mm	3.4mm	10.0mm	M3	24A
CTSN434/12M	12mm/16A	141.9mm	23.2mm	19.2mm	3.3mm	4.3mm	12.0mm	M3.5	57A
CTSN434/12F	12mm/16A	141.9mm	23.2mm	19.2mm	3.3mm	4.3mm	12.0mm	M3.5	57A