

MNX PCM 150/75 T



Sample photo

Order symbol: PCM 150/75 T
Product nbr: 6016914
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN:	6418074038258
El. number:	
Finland:	3421666
Electric No.	8212027174
Denmark:	
Electric No. Italy:	7342045
Electric No. Sweden:	2535427

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	180	130	75
inch:	7.1	5.1	3.0

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	Smoked grey
Cover screws colour:	Black
Gasket material:	TPE

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:

MIV 150	Mounting plate (Galvanized steel)
---------	-----------------------------------

Accessories:

MIN 10	DIN-15 Mounting rail
MIN 15	DIN-15 Mounting rail
MIV 10	DIN-35 Mounting rail
MIV 15	DIN-35 Mounting rail
FP A 150/180	Front plate (Aluminium)
HFP 180	Front plate hinge series
FP 22046	Wall fastening lug (4 pcs)

Rating:

Ingress Protection (EN 60529): IP66/67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 6

Certificates:

Germanischer Lloyd (GL)
SGS Fimko
Gost R

