

**Error! No topic specified.**

### FEATURES:

- BNC Cable breakouts to Minigrabber® Test Clips for test versatility.
- BNC connector and breakout wires are molded directly to the cable for added pull strength.
- Grabber hook attaches to terminal sizes up to .060" (1,5mm)
- Schematic: Black Grabber to BNC Shell, Red Grabber to BNC Center Contact.

### MATERIALS:

BNC: Body: Brass, Nickel Plated, Center Pin: Brass, Gold Plated, Impedance: 50 Ohms

Strain Relief and Molded Breakout: PVC, Color: Black

Breakout Wires: 20 AWG Stranding 41 x 36 t. c., PVC Insulated, .087" (2,21 mm) O.D.,  
Color Matches Grabbers

Cable: "C" Cable: RG58C/U, .195" (5.0mm) O.D., Color: Black, 20AWG (Strand 19 x .0071 t.c.)

"K" Cable: RG174/U, .100" (2.5mm) O.D., Color: Black, 26 AWG (Strand 7 x 34 Bare Copper)

Marking "POMONA" 5187-C-XX" or "5187-K-XX"

Grabber: Contact – Beryllium Copper, Gold Plated

Spring – Stainless Steel

Insulation – Glass Filled Nylon. Color: one red, one black

### RATINGS:

Operating Voltage: 300 VRMS

Operating Temperature: 50°C (+122°F) Max.

### ORDERING INFORMATION: Model 5187-Cable Code- Length in Inch

Cable Code: -C = RG58C/U, -K = RG174/U, XX = Lengths in Inches, Std. Lengths: 24" (60,96 cm), 36" (91,44 cm), 48" (121,92 cm) & 60" (152,40 cm) Additional lengths are available upon request.

Ordering Example: 5187-C-36, Cable will be 36" (91,44cm) of RG58C/U.