



Ethernet Switch

Ha-VIS mCon 7050-B1V

5-port Ethernet Switch with extended input voltage range for industrial Ethernet networks, with M12 system cabling

Managed	IP65 / IP67	PROFINET compatible 	EtherNet/IP compatible 
Number of ports, Copper / Termination	5x 10/100Base-T(X) / M12 D-coding (female)		
Input voltage / Termination	24 / 48 V DC / M12 A-coding, male, for redundant power supply		
Permissible range (min./max.)	12 V ... 60 V DC		
Input current	approx. 160 mA (at 24 V DC)		
Housing material	zinc die-cast		
Dimensions (W x H x D)	45 x 120 x 87 mm		
Weight	approx. 0.8 kg		
Working temperature	-40 °C ... +70 °C		
Approvals	e1		
MTBF	462.000 h		
Management	fully managed via Web interface and SNMP Functions see pages 01.141 and 01.142		

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS mCon 7050-B1V Ethernet Switch with 5 ports M12 D-coding	20 70 305 4943		