

PART NAME	NON-METALLIC ENCLOSURE (STYLE B)	PART No.	NBB-10241 & NBB-10261 & NBB-22241	REV. DATE	10-28-14
-----------	----------------------------------	----------	-----------------------------------	-----------	----------

ALL ENCLOSURES MEET NEMA TYPE 1, 2, 4, 4X, 12 & 13 AND IEC529-IP65

SUPPLIED WITH (4) SMALL WALL MOUNTING BRKTS. (REF. NBX-10920) & (4) M5x0.8 x 12mm LG. TRUSS HD. SELF-TAPPING SCREWS (NOT SHOWN)

INTERNAL HINGED PANEL MOUNTING BRACKETS, STAINLESS STEEL LOCKING HASP, AIR AND MOISTURE VENTS AND GALVANIZED STEEL INTERNAL PANEL ARE NOT INCLUDED, BUT CAN BE PURCHASED SEPARATELY.

MATERIAL:

UL508-4X INDOOR VERSION

SOLID BODY & COVER _____ LIGHT GRAY ABS/PC BLENDED PLASTIC
UL94-5VB FLAMMABILITY RATING

CLEAR COVER _____ POLYCARBONATE PLASTIC
UL94V-0 FLAMMABILITY RATING
UV STABILIZED

ABS VERSION

SOLID BODY & COVER _____ LIGHT GRAY ABS
UL94-HB FLAMMABILITY RATING

LATCHES & HINGES _____ NON-METALLIC

WALL MOUNTING BRACKETS _____ STAINLESS STEEL

COVER INCLUDES GRAY POLYURETHANE GASKET.

0.275 [7] DIA. BOSS WITH 0.137 [3] DIA. HOLE 0.255 [6] DEEP (8) PLACES -SEE NOTE

0.500 [13] DIA. BOSS WITH 0.137 [3] DIA. HOLE 0.255 [6] DEEP (6) PLACES - SEE NOTE

0.500 [13] DIA. BOSS WITH M4x0.7 THREADED BRASS INSERT (2) PLACES

VIEW LESS COVER

NOTE:
BOSSES ACCEPT M4 METRIC OR #8 STD. SHEET METAL SCREWS x 0.250 [6] LG. (NOT SUPPLIED)

DIMENSIONS = INCHES
[MILLIMETERS]

NOTE: ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE UNLESS OTHERWISE SPECIFIED

UL508-4X INDOOR VERSION		ABS VERSION																					
PART NO.		PART NO.																					
SOLID COVER	CLEAR COVER	SOLID COVER	DIMENSIONS																				
			A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	S	T	U	V	W	
NBB-10241	NBB-10261	NBB-22241	6.780 [172]	6.000 [152]	5.350 [136]	4.352 [111]	4.138 [105]	2.765 [70]	10.750 [273]	9.940 [252]	9.294 [236]	8.085 [205]	7.896 [201]	5.129 [130]	3.142 [80]	1.190 [30]	10.100 [257]	10.090 [256]	6.140 [156]	6.150 [156]	8.283 [210]	4.330 [110]	