


THIS DOCUMENT CONTAINS DATA PROPRIETARY
TO PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC.
IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	5	V _{p-p}
OPERATING VOLTAGE RANGE	1 ~ 25	V _{p-p}
RATED CURRENT (MAX)	5	mA
CAPACITANCE	16,000±30%	pF
MINIMUM SPL @ 10 CM	75	dBA
RESONANT FREQUENCY	4,100	Hz
OPERATING TEMPERATURE	-40 ~ +105	°C
STORAGE TEMPERATURE	-40 ~ +105	°C
HOUSING MATERIAL	LCP	—
TERMINAL MATERIAL	TIN-PLATED PHOSPHOR BRONZE	—
WEIGHT	0.6	grams



FILE NAME
SMT-1325.DWG

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE
OR WITHDRAWAL WITHOUT NOTICE.

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	1/28/05	

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN R. A. C.	1/05
CHECKED B. R.	1/05
APPROVED R. W.	1/05
DO NOT SCALE DRAWING	

projects®
unlimited

Dayton, Ohio

SURFACE MOUNT TRANSDUCER (PIEZO)
SMT-1325

SIZE A	DRAWING NO. SMT-1325
SCALE: N.T.S.	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMT-1325](#)