

13

Electricians' Pliers



13 01 160




13 02 160



- ▶ the ideal plier for cable work
- ▶ for gripping and bending wire
- ▶ for cutting soft, medium and hard wire
- ▶ precision cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- ▶ with precision stripping holes
- ▶ for crimping end sleeves (ferrules)
- ▶ high grade special tool steel, oil-hardened and tempered

Model 13 01 614:


- ▶ for AWG 10/12/14




Gripping



Cutting



Stripping



Crimping

Article-No.	EAN-	Head	Handles	Stripping capacities		
Length	Code					
mm/Zoll	4003773-			mm ²	AWG	g
13 01 160	010210	polished	plastic coated	0.5-0.75/1.5/2.5		110
13 01 614	040231	polished	plastic coated		10/12/14	110
13 02 160	010470	polished	with two-colour dual component handles	0.5-0.75/1.5/2.5		150

13

Universal Plier for Data Cable, STP



13 72 160 SB

- ▶ for cutting the whole cable, the single conductor, the shield and the plastic core
- ▶ steel point at the joint for longitudinal scratching of the shield foil
- ▶ prismatic blades below the joint for dismantling the cables
- ▶ special tool steel, oil-hardened

Article-No.	EAN-	Head	Handles	
Length	Code			
mm	4003773-			g
13 72 160 SB	052319	burnished	with two-colour dual component handles	80



Smooth and clean dismantling of data cables