

Heyco® Thick Panel Glossy Plugs

Multiple Locking Steps for Panel Thickness up to .250" (6,4 mm)

Mounting Hole Diameter Range: .500" (12,7 mm) to 2.000" (50,8 mm)




MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS			
in.	mm.	Black	White		A		B	
					Head in.	Diameter mm.	Overall in.	Height mm.
.500	12,7	2430	2431	GPT 500	.563	14,3	.562	14,3
.625	15,9	3134	3135	GPT 625*	.720	18,3	.515	13,1
.750	19,1	3136	3137	GPT 750*	.850	21,6		
.875	22,2	3138	3139	GPT 875	.953	24,2	.562	14,3
1.000	25,4	3140	3141	GPT 1000	1.125	28,6		
1.093 - 1.125	27,8 - 28,6	3142	3143	GPT 1093	1.218	30,9		
1.187	30,1	3144	3145	GPT 1187	1.312	33,3		
1.375	34,9	2432	2433	GPT 1375	1.486	37,7		
1.500	38,1	2428	2429	GPT 1500	1.609	40,8		
1.750	44,4	2436	2437	GPT 1750	1.875	47,6		
2.000	50,8	2438	2439	GPT 2000	2.157	54,8		


Standard color black. Consult Heyco for other colors.

*Single locking step for Panel Thickness up to .250" (6,4 mm).

- For use in panels thicker than .125" (3,2 mm).
- Smooth, glossy head provides easy glide and shiny finish.
- Close unneeded panel holes and electrical knock-outs.
- Locking fingers snap into holes with fingertip pressure for quick and easy installation.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Withstand a push back force of 35 pounds.
- Available in multiple sizes for use in .500" (12,7 mm) to 2.000" (50,8 mm) diameter holes.



SINGLE PANEL THICKNESS



MULTIPLE PANEL THICKNESS

Material
Certifications

Nylon 6/6

Recognized under the Component Program of Underwriters' Laboratories, File E51579

Certified by Canadian Standards Association, File 8919

Flammability Rating
Temperature Rating

94V-2

-40°F (-40°C) to 221°F (105°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1299](#)