



MATERIAL NO.	ENGINEERING NO.	LENGTH
1300080315	303001P80M050	16' 5" +6.50-0 (5M +16.5cm-0)
1300080316	303001P80M100	32' 10" +12.50-0 (10M +31.8cm-0)




Partial1
Scale 1.5:1

WIRING DIAGRAM	P1
VIOLET	1
RED	2
GRAY	3
RED/BLUE	4
BLUE (-VE)	5
GREEN	6
BROWN (+VE)	7
WHITE/GREEN	8
WHITE/YELLOW	9
WHITE/GRAY	10
BLACK	11
YELLOW/GREEN (GRD)	12
YELLOW/BROWN	13
BROWN/GREEN	14
WHITE	15
YELLOW	16
PINK	17
GRAY/BROWN	18
GRAY/PINK	19



- NOTES:
- 1. MATERIAL: SEE TABLE
 - 2. FINISHES: SEE TABLE
 - 3. MATES WITH: 19 POLE MALE MINI-CHANGE
 - 4. ELECTRICAL SPECIFICATIONS:
 - VOLTAGE RATING: 300V AC/DC
 - CURRENT RATING: 3 AMPS (18 AWG)
 - 2 AMPS (22 AWG)
 - 5. ASSEMBLY IS RoHS COMPLIANT



LENGTH
(SEE CHART)

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
7	1	OVERMOLD	PVC	YELLOW
6	1	COUPLING NUT, C-SIZE	DIE CAST ZINC	BLACK
5	1	FRICTION RING, C-SIZE	NYLON	WHITE
4	16	FEMALE CONTACT	Cu ALLOY	GOLD PLATED
3	3	FEMALE CONTACT/SLEEVE ASSY	BRASS/SS	GOLD PLATED
2	2	INSERT, FEMALE, 19 POLE	PVC	YELLOW
1	1	CABLE, 3 X 0.75mm ² (18 AWG) + 16 X 0.34mm ² (22 AWG)	PUR OUTER JACKET	BLACK

RELEASED
EC NO: WNAZ010-0046
2009/07/21
DRAWN BY: DRWINSTONE
CHKD BY: WOODMAN
APPR: JF MURPHY
2009/08/10

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± ---
2 PLACES ± ---	± .01
1 PLACE ± 0.3	± ---
ANGULAR ± 1/2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
IN/MM	
DRAWN BY	DATE
R.STONE	2009/07/20
CHECKED BY	DATE
B.WOODMAN	2009/07/22
APPROVED BY	DATE
J.MURPHY	2009/07/25
MATERIAL NO.	
SEE CHART	
SIZE	C

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
1.5:1	INCH	☉
TITLE		
MINI-CHANGE 19 POLE FEMALE, STRAIGHT CABLE ASSY, EURO MARKET		
MOLEX INCORPORATED		
DOCUMENT NO.		SHEET NO.
SD-130008-009		1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		