


## UT 4-MTD-PE/S

Order No.: 3046207



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3046207>

Feed-through modular terminal block, Connection type: Screw connection, Cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, AWG: 26 - 10, Length: 57.8 mm, Width: 6.2 mm, Color: green-yellow, Assembly: NS 35/7.5, NS 35/15



### Commercial data

|                          |                   |
|--------------------------|-------------------|
| GTIN (EAN)               | 4017918956608     |
| sales group              | A803              |
| Pack                     | 50 pcs.           |
| Customs tariff           | 85369010          |
| Weight/Piece             | 0.027148 KG       |
| Catalog page information | Page 57 (CL-2009) |

### Product notes

WEEE/RoHS-compliant since: 01/01/2003



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Certificates / Approvals



Certification

CB, CSA, CUL, DNV, GL, LR, UL, VDE-PZI

Certification Ex: IECEX, KEMA-EX

#### CSA

|           |       |
|-----------|-------|
| AWG/kcmil | 26-10 |
|-----------|-------|

#### CUL

|           |       |
|-----------|-------|
| AWG/kcmil | 26-10 |
|-----------|-------|

#### UL

|           |       |
|-----------|-------|
| AWG/kcmil | 26-10 |
|-----------|-------|

#### Accessories

| Item            | Designation                 | Description                                                                                                                                                                                                                  |
|-----------------|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Assembly</b> |                             |                                                                                                                                                                                                                              |
| 3022276         | CLIPFIX 35-5                | Snap-on end bracket, for NS 35/7.5 or NS 35/15 DIN rail, can be fitted with Zack strip ZB 5 and ZBF 5, terminal strip marker KLM 2 and KLM, parking facility for FBS...5, FBS...6, KSS 5, KSS 6, width: 5,15 mm, color: gray |
| 0801762         | NS 35/ 7,5 CU UNPERF 2000MM | DIN rail, material: Copper, unperforated, height 7.5 mm, width 35 mm, length: 2 m                                                                                                                                            |
| 1207640         | NS 35/ 7,5 PERF 755MM       | NS 35 DIN rail, height 7.5 mm, length 755 mm                                                                                                                                                                                 |
| 1207653         | NS 35/ 7,5 PERF 955MM       | NS35 DIN rail, height 7.5 mm, length 955 mm                                                                                                                                                                                  |
| 1207666         | NS 35/ 7,5 PERF 1155MM      | NS 35 DIN rail, height 7.5 mm, length 1155 mm                                                                                                                                                                                |
| 0801733         | NS 35/ 7,5 PERF 2000MM      | DIN rail, material: Steel, galvanized and passivated with a thick layer, perforated, height 7.5 mm, width 35 mm, length: 2 m                                                                                                 |
| 0801681         | NS 35/ 7,5 UNPERF 2000MM    | DIN rail, material: Steel, unperforated, height 7.5 mm, width 35 mm, length: 2 m                                                                                                                                             |
| 1201756         | NS 35/15 AL UNPERF 2000MM   | DIN rail, deep-drawn, high profile, unperforated, 1.5 mm thick, material: Aluminum, height 15 mm, width 35 mm, length 2 m                                                                                                    |
| 1201895         | NS 35/15 CU UNPERF 2000MM   | DIN rail, material: Copper, unperforated, 1.5 mm thick, height 15 mm, width 35 mm, length: 2 m                                                                                                                               |
| 1207679         | NS 35/15 PERF 755MM         | NS 35 DIN rail, perforated, height 15 mm, length 755 mm                                                                                                                                                                      |
| 1207682         | NS 35/15 PERF 955MM         | NS 35 DIN rail, perforated, height 15 mm, length 955 mm                                                                                                                                                                      |
| 1207695         | NS 35/15 PERF 1155MM        | NS 35 DIN rail, perforated, height 15 mm, length 1155 mm                                                                                                                                                                     |
| 1201730         | NS 35/15 PERF 2000MM        | DIN rail, material: Steel, perforated, height 15 mm, width 35 mm, length: 2 m                                                                                                                                                |
| 1201714         | NS 35/15 UNPERF 2000MM      | DIN rail, material: Steel, unperforated, height 15 mm, width 35 mm, length: 2 m                                                                                                                                              |
| 1201798         | NS 35/15-2,3 UNPERF 2000MM  | DIN rail, material: Steel, unperforated, 2.3 mm thick, height 15 mm, width 35 mm, length: 2 m                                                                                                                                |

#### Marking

|         |                         |                                                                                                                                               |
|---------|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| 1051993 | B-STIFT                 | Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm                                   |
| 0811228 | X-PEN 0,35              | Marker pen without ink cartridge, for manual labeling of markers, labeling extremely wipe-proof, line thickness 0.35 mm                       |
| 1051016 | ZB 6,LGS:FORTL.ZAHLEN   | Zack marker strip, 10-section, printed horizontally: with the numbers 1 - 10, 11 - 20 and so on up to 491 - 500, color: white                 |
| 1051032 | ZB 6,LGS:GLEICHE ZAHLEN | Zack marker strip, printed horizontally: 10-section, with identical numbers 1/1/1, 2/2/2, and so on up to 100, color: white                   |
| 1051029 | ZB 6,QR:FORTL.ZAHLEN    | Zack marker strip, 10-section, printed vertically: with consecutive numbers 1 - 10, 11 - 20, and so on up to 491 - 500, color: white          |
| 1051045 | ZB 6,QR:GLEICHE ZAHLEN  | Zack marker, labeled vertically: 10-section, with identical numbers, 1/1/1, 2/2/2 etc. up to 1000/1000/1000, color: White                     |
| 1050499 | ZB 6:SO/CMS             | Zack strip, 10-section, divisible, special printing, marking according to customer requirements                                               |
| 1051003 | ZB 6:UNBEDRUCKT         | Zack strip, unprinted, strips with 10 labels for individual labeling with M-PEN or CMS system, for terminal block width: 6.2 mm, color: white |

#### Plug/Adapter


|         |           |                                 |
|---------|-----------|---------------------------------|
| 0201731 | MPS-IH BK | Insulating sleeve, Color: black |
| 0201702 | MPS-IH GN | Insulating sleeve, Color: green |
| 0201676 | MPS-IH RD | Insulating sleeve, Color: red   |
| 0201663 | MPS-IH WH | Insulating sleeve, Color: white |
| 0201744 | MPS-MT    | Test plugs                      |

#### Tools

|         |             |                                                                                                                                                                  |
|---------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1205053 | SZS 0,6X3,5 | Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip |
|---------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|

#### Diagrams/Drawings

Circuit diagram



**Address**

PHOENIX CONTACT Inc., USA  
586 Fulling Mill Road  
Middletown, PA 17057, USA  
Phone (800) 888-7388  
Fax (717) 944-1625  
<http://www.phoenixcon.com>



© 2010 Phoenix Contact  
Technical modifications reserved;