

Technical data



Material : Polyvinylchloride (hard PVC)

Colour : grey RAL 7030

Operating temperature : static -20 °C bis +60 °C
: dynamic -5 °C bis +60 °C

Working temperature : > 0 °C

Typical values

Test method

Specific weight : 1,5 kp / cm³

Flammability : self-extinguishing V0
Fire load : 5,2 kW / kg

UL 94

Silicone : not included

Lead : not included

Cadmium : not included

Dielectric strength : 450 kV/cm

UV resistance : PVC has a limited UV resistance, colour changes are not excluded by UV exposure

Specification : UL, VDE, EN50085-2-3

Available length : 2 m incl. Cover