

**Part Number: 85502-5036**

Image not available

Status: Active - Custom
Series: [85502](#)
Category: Molex Parts

Series image - Reference only

Product Environmental Compliance

[EU RoHS:](#) ELV and RoHS Compliant[China RoHS:](#) [REACH SVHC:](#) Contains SVHC: No[Low-Halogen Status:](#) Not Reviewed

Part Detail

General

Status

Category

Series

Physical

Flammability 94V-0

Agency Certification

UL E107635

Solder Process Data

Duration at Max. Process Temperature (seconds)	45
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

Material Info

UPC 822350901581

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)