

# 30W High power LED Flood Light


---

## Specifications:

Commodity	30W led flood lighting
Input Voltage	AC85-265V
Frequency Range	50~60Hz
Power Factor (PF)	>0.9
Lamp's Efficiency (%)	> 90%
Colour	White
Colour Temperature	2700-3500K/6000-6500K
Power	30W
Lumens	2400-2700LM
Type of LED	Epistar
Beam Angle	120°-140°/60°
Color Index(CRI)	Ra > 80
Working Temperature	(-30 °C) ~ ( 45 °C)



## Dimensions:



## Applications:

**Floodlighting and wall washing for bars, clubs, hotels, stages, parks, squares, commercial buildings facade, museums, and art galleries, historical buildings.**

