



(2,00 mm) .0787"

T2M-105-01-L-D-RA-WT

T2M-110-01-L-D-TH-WT-DS

T2M-105-01-L-D-TH-WT

T2M-105-01-L-D-SM-WT

T2M SERIES

HIGH RELIABILITY CABLE HEADER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?T2M

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over

50µ" (1,27 µm) Ni

Current Rating (T2M/S2SD):

3.8 A per pin

(1 pin powered per row)

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:

Yes

Processing:


Lead-Free Solderable:

Yes


SMT Lead Coplanarity:

(0,10 mm) .004" max

Mates with:
S2SD, S2M, S2SDT



MATED HEIGHT



Mates with Tiger Eye™ discrete wire cable assemblies

Up to 30 positions per row

Choice of Surface Mount, Through-hole or Right Angle

Optional weld tab

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



OTHER SOLUTIONS



See S2SD in the discrete wire section or contact Samtec.

ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.

