






SECTION A-A



- 1 MARK AMP, PART NO., DATE CODE
 2 NUMBERS INDICATING END POSITIONS MARKED THIS SIDE ONLY.
 3 .00030 GOLD IN CONTACT AREA, SELECTIVE OVER NICKEL TIN ON CONTACT TAILS. CONTACT MATL: BRASS.
 4 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER MIL-M-24519, GLCP-30F; COLOR: GRAY.
 5 FEATURE NOT PRESENT IN 20 THRU 50 POSITION.



CARD EDGE -

RECOMMENDED PRINTED CIRCUIT BOARD LAYOUT
(CONNECTOR SIDE)

1-10	450 [11.43]	9	1,150 [29.21]	900 [22.86]	20	1-530733-1
1-15	700 [17.78]	14	1,400 [35.56]	1,150 [29.21]	30	1-530733-0
1-64	3,150 [80.01]	63	3,850 [97.79]	3,600 [91.44]	128	530733-9
1-55	2,700 [68.58]	54	3,400 [86.36]	3,150 [80.01]	110	530733-8
1-50	2,450 [62.23]	49	3,150 [80.01]	2,900 [73.66]	100	530733-7
1-45	2,200 [55.88]	44	2,900 [73.66]	2,650 [67.31]	90	530733-6
1-40	1,950 [49.53]	39	2,650 [67.31]	2,400 [60.96]	80	530733-5
1-35	1,700 [43.18]	34	2,400 [60.96]	2,150 [54.61]	70	530733-4
1-30	1,450 [36.83]	29	2,150 [54.61]	1,900 [48.26]	60	530733-3
1-25	1,200 [30.48]	24	1,900 [48.26]	1,650 [41.91]	50	530733-2
1-20	950 [24.13]	19	1,650 [41.91]	1,400 [35.56]	40	530733-1
	Z	Y	X	U	NO OF CONTACTS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.WIEST 9-12-89		 TE Connectivity				SHEET NO. 1	
		CHK D.GUTTER 11-20-91							
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY,PIN HEADER, MINI-BOX RIGHT ANGLE —					
		APVD D.GUTTER 11-20-91							
		PRODUCT SPEC —							
		APPLICATION SPEC —							
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
				WEIGHT 0	A2	00779	G-530733		—
CUSTOMER DRAWING						SCALE NTS	SHEET 1 of 1		REV F