

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material  
- Favorite Products List  
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) [Search Tips](#)

**Text Search: 'F512D6-6F26Y'**

Your search criteria matched only one product, shown below

**F512D6-6F26Y**



- Pass all TIA/EIA-568-B.3 performance requirements
- FOCIS-5 compliant
- Insertion loss per mated pair: 0.50dB typical; 0.75dB max.
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode cable assembly
- Lifetime traceability of test data to a Q.C. number on each cable assembly

\* MTP is a registered trademark of US Conec Ltd.

▪ Part Number	F512D6-6F26Y
▪ RoHS Compliance Status	Compliant
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS
▪ Part Description	Male MTP* to male MTP* 12-fiber interconnect cable assembly (one male MTP* connector on each end on ribbon interconnect cable) – 50/125µm. Outside diameter: 5mm x 2.5mm.
▪ Product Type	MTP* Interconnect Cable Assemblies
▪ Length (ft.)	26
▪ Fiber Compatibility	50/125µm
▪ Fiber Cable Size	5mm x 2.5mm
▪ Fiber Type	Multimode
▪ Connector 1 Type	Male MTP*
▪ Connector 2 Type	Male MTP*
▪ Fiber Count	12
▪ Flammability Rating	Plenum (OFNP)
▪ Pricing Description	Male MTP*- Male MTP* Ribbon Interconnect Cable Assembly OM2 50µm, OFNP, 26ft
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.