



English | 简体中文 | 日本語

Search Entire Site [GO](#)

[Contact IDT](#) | [Investors](#) | [Press](#)

[About IDT](#)

[Products](#)

[Applications](#)

[Support](#)

[myIDT](#)

[Document Search](#) | [Package Search](#) | [Parametric Search](#) | [Cross Reference Search](#) | [Green & RoHS](#) | [Calculators](#) | [Thermal Data](#) | [Reliability & Quality](#) | [Military](#)

[Home](#) > [Products](#) > > [SSTUB32866C](#) > [SSTUB32866CHLFT](#)

[Add to myIDT \[?\]](#)

You may also like...

SSTUB32866CHLFT

Category:

Generic Part:

Market Group:

Description:

SSTUB32866C

RDIMM

1.8V REG. BUFFER (800 MHZ)

**Time is
money**

Parameters

Package	CABGA 96 (BFG96)
Speed	NA
Temperature	C
Voltage	3.3 V
Status	Active
Sample	No
Minimum Order Quantity	2500
Factory Order Increment	2500

Package

Description	CHIP ARRAY BGA 5.5 X 13.5 MM X 0.8 MM PI
Class	PLASTIC
Moisture Sensitivity Level (MSL)	3
Category	Green
Moisture Exposure Floor Life	168 hrs. @ <30°C/60%RH
Peak Reflow Temperature	260°C
Rebake Conditions	48 hrs.@125°C
Length	13.5
Mark	H
Width	5.5
Pitch	0.8
Thickness	1.4
Status	Active

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Product Change Notice	PCN# : A-0607-02 IDT Penang as Alternate Assembly Facility for ICS CVBGA and FPBGA	100 KB	07/27/2006
	PCN# A-0607-05 Green Mold Compound KMC3580 for BGA	195 KB	08/30/2006
	PCN# : A-0610-02 ASAT China as Alternate Facility for CABGA/CV BGA/FPBGA/TQFP/PQFP	253 KB	10/19/2006

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) What is this?

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. [All Rights Reserved](#).