

AMPHENOL RF PART NUMBER

031-3212

BNC Straight Clamp Plug for RG-59, RG-62, RG-140, 210, 50 Ohm



PRODUCT OVERVIEW

RF Connector, BNC Straight Clamp Plug for RG-59, RG-62, RG-140, 210, 50 Ohm

Product Type	Connectors
Product Series	BNC
Status	Active

PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Clamp
Impedence (Ohms)	50
Body Finish	Nickel
Body Material	Brass
Contact Finish	Silver
Contact Material	Brass
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	E
Cable Type	Belden 8241, Belden 8263, Belden 8279, Belden 9209, RG-140, RG-210, RG-59, RG-59B, RG-62
Coupling Mechanism	Bayonet
Max Frequency (GHz)	4
Polarity	Standard
Min. Temp. (Celsius)	-65

Max. Temp. (Celsius)	165
Mating Cycles	500
Military Qualified	Yes
Military Part Number	UG-260D/U
Weight (Grams)	14.514

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------