

NOTES:

- ① MAT'L: COPPER
PLATING: ELECTRO TIN (.0003 MIN)
TIN-PLATED BRASS FUNNEL FERRULE
- ②
- ③ NYLON INSULATION (COLOR CODED RED)

STUD SIZES: (£.005)

02 = .094

04 = 119

 $06 = .146$

08 = 173

10 = 198

14 = 265

56 = 328


38 = 390

"UL" LISTING # E32244

"CSA" LISTING #18689

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

(MWID) = DENOTES MAXIMUM WIRE INSULATION DIAMETER



WIRE SIZE: 22-18 AWG²
.25-1.5 MM²

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	"ID" MIN.	DATE	TITLE:	STOCK THICKNESS
AA-8109 -	$\frac{.187}{4.75}$	$\frac{.183}{4.65}$	$\frac{.727}{18.47}$	$\frac{.054}{1.37}$	11-8-84	SPADE TONGUE TERMINAL AVIKRIMP 800-SERIES	$\frac{.031 \pm .001}{.79}$
					DRWN. BY: JJ		
					11-14-87		
							</