


datasheet for PK 10 A  
article number: 930099101



|                                  |                                                                                                                                                                                                       |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>product description:</b>      | <b>order number: 930 099-101</b>                                                                                                                                                                      |
| <b>description:</b>              | Pole terminal with claw edge and captive insulated head. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For installation in equipment chassis and switch panels. |
| <b>typ:</b>                      | PK 10 A rot/red                                                                                                                                                                                       |
| <b>system:</b>                   | 4 mm system                                                                                                                                                                                           |
| <b>order number:</b>             | 930 099-101                                                                                                                                                                                           |
| <b>color</b>                     |                                                                                                                      |
| <b>other color versions:</b>     |                                                                                                                     |
| <b>technical data</b>            |                                                                                                                                                                                                       |
| <b>type of contact:</b>          | spring loaded socket                                                                                                                                                                                  |
| <b>type of termination:</b>      | M 4 thread                                                                                                                                                                                            |
| <b>rated voltage:</b>            | DC 60 V                                                                                                                                                                                               |
| <b>rated current:</b>            | 16 A                                                                                                                                                                                                  |
| <b>contact resistance:</b>       | 2 mOhm                                                                                                                                                                                                |
| <b>mounting:</b>                 | screw                                                                                                                                                                                                 |
| <b>material</b>                  |                                                                                                                                                                                                       |
| <b>contact material:</b>         | brass                                                                                                                                                                                                 |
| <b>contact surface material:</b> | nickel-plated                                                                                                                                                                                         |
| <b>housing material:</b>         | PF                                                                                                                                                                                                    |
| <b>environmental conditions:</b> |                                                                                                                                                                                                       |
| <b>temperature range:</b>        | -25 °C to +100 °C                                                                                                                                                                                     |
| <b>flammable class:</b>          |                                                                                                                                                                                                       |
| <b>housing:</b>                  | 94 V-0                                                                                                                                                                                                |
| <b>drawing</b>                   |                                                                                                                   |