

HC-D 7-TFL-57/O1M20G/PA

Order No.: 1604889

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1604889>

HEAVYCON sleeve housing D7, for single locking latch, height 57 mm, with support, straight conductor exit, PA

Commercial data

GTIN (EAN)	 4 017918 881047
sales group	D011
Pack	10 pcs.
Customs tariff	85472000
Catalog page information	Page 508 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Note	For contact inserts HC-D7, D8, A3, A4, B5, HS2-D7
Design	D7
Height	57 mm

Width	28 mm
Length	26.5 mm
Housing type	Sleeve housings
Locking type	for single locking latch
Cable exit	Straight
Type of the screw connection	1x M20
Degree of protection	IP54 / IP65 with sealing screw
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	PA
Housing surface material	PA, light gray
Material lock	PA

Certificates / Approvals



Certification


GOST

Accessories

Item	Designation	Description
Assembly		
1686229	HC-D 7-DS-IP65	Sealing screw, for IP65 protection
General		
1647967	HC-M-DE-M20	Pressure screw set, for housing with M20 thread, consisting of notched seal, 2 washers and pressure screw

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;